

Part No: YS2BC8-020C

Filters & Strainers

Y-Strainers

Desc: 2 CPVC T/U Y STRAINER FPT EPDM C8 MESH

MSRP: 1265.33

Part Code: 104

Weight(lbs): 4.76

Weight(kg): 2.159

Weight(gm): 2159

Size: 2"

Color: GRAY

Material: CPVC

Connection Fipt - True Union

O-Ring EPDM

Mesh Sieve # 8

Body Color Gray



A = 8-15/16

A1 = 12-7/16

B = 10-13/16

C = 12-13/16

D = 6-3/16

E = 3-1/2

Injection Molded Dimension References:

G = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses; $\pm 1/32$ inch.

H = Intersection of center lines to face of fitting; 90° elbows tees, crosses; $\pm 1/32$ inch.

J = Intersection of center lines to bottom of socket/thread; 45° elbows; $\pm 1/32$ inch

L = Overall length of fittings; $\pm 1/16$ inch.

M = Outside diameter of socket/thread hub; $\pm 1/16$ inch.

N = Socket bottom to socket bottom; couplings; $\pm 1/16$ inch.

W = Height of cap; $\pm 1/16$ inch

Typical Molded Dimension References

