

Part No: YS31C8-005CSR

Filters & Strainers

Y-Strainers

Desc: 1/2 CPVC Y STRAINER SR/FPT FKM C8 MESH

MSRP: 450.9

Part Code: 104

Weight(lbs): 0.375

Weight(kg): 0.17

Weight(gm): 170

Size: 1/2"

Color: GRAY

Material: CPVC

Connection SR Fipt

O-Ring FKM

Mesh Sieve # 8

Body Color Gray



A = 3- 1/16

A1 = 4- 7/8

B = 3- 5/8

C = 5- 1/16

D = 2- 1/2

E = 1- 5/8

Cv = 5.5
Values

Injection Molded Dimension References:

G = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses; ± 1/32 inch.

H = Intersection of center lines to face of fitting; 90° elbows tees, crosses; ± 1/32 inch.

J = Intersection of center lines to bottom of socket/thread; 45° elbows; ± 1/32 inch

L = Overall length of fittings; ± 1/16 inch.

M = Outside diameter of socket/thread hub; ± 1/16 inch.

N = Socket bottom to socket bottom; couplings; ± 1/16 inch.

W = Height of cap; ± 1/16 inch

Typical Molded Dimension References

