

Part No: YS31P8-030CLSR

Filters & Strainers

Y-Strainers

Desc: 3 PVC CL Y STRAINER SR/FPT FKM P8 MESH

MSRP: 1009.21

Part Code: 103

Weight(lbs): 6.837

Weight(kg): 3.101

Weight(gm): 3101

Size: 3"

Color: CLEAR

Material: PVC

Connection SR Fipt

O-Ring FKM

Mesh Sieve # 8

Body Color Clear



A = 9-11/16

A1 = 15- 5/16

B = 11

C = 14- 1/4

D = 7- 5/8

E = 5- 1/8

Cv = 75.2
Values

Injection Molded Dimension References:

G = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses; ± 1/32 inch.

H = Intersection of center lines to face of fitting; 90° elbows tees, crosses; ± 1/32 inch.

J = Intersection of center lines to bottom of socket/thread; 45° elbows; ± 1/32 inch

L = Overall length of fittings; ± 1/16 inch.

M = Outside diameter of socket/thread hub; ± 1/16 inch.

N = Socket bottom to socket bottom; couplings; ± 1/16 inch.

W = Height of cap; ± 1/16 inch

Typical Molded Dimension References

