

Part No: YS32P8-040

Filters & Strainers

Y-Strainers

Desc: 4 PVC Y STRAINER SOC FKM P8 MESH

MSRP: 1639.59

Part Code: 102

Weight(lbs): 9.947

Weight(kg): 4.512

Weight(gm): 4512

Size: 4"

Color: GRAY

Material: PVC



Connection Socket

O-Ring FKM

Mesh Sieve # 8

Body Color Gray

A = 12- 1/2

A1 = 19-11/16

B = 8- 5/8

C = 13- 1/8

D = 9- 7/8

E = 6- 9/16

Cv = 169.5
Values

Injection Molded Dimension References:

G = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses; ± 1/32 inch.

H = Intersection of center lines to face of fitting; 90° elbows tees, crosses; ± 1/32 inch.

J = Intersection of center lines to bottom of socket/thread; 45° elbows; ± 1/32 inch

L = Overall length of fittings; ± 1/16 inch.

M = Outside diameter of socket/thread hub; ± 1/16 inch.

N = Socket bottom to socket bottom; couplings; ± 1/16 inch.

W = Height of cap; ± 1/16 inch

Typical Molded Dimension References

