

Part No: YS33S8-007CL

Filters & Strainers

Y-Strainers

Desc: 3/4 PVC CL Y-STRAINER FLANGED FKM S8MESH

MSRP: 605.34

Part Code: 103

Weight(lbs): 1.034


Weight(kg): 0.469

Weight(gm): 469

Size: 3/4"

Color: CLEAR

Material: PVC



Connection Flanged

O-Ring FKM

Mesh Sieve # 8

Body Color Clear

A = 5- 1/16

A1 = 7- 1/8

B = 6- 7/16

C = 3- 7/8

D = 3- 1/8

E = 2

Cv = 8.2
Values

Injection Molded Dimension References:

G = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses; ± 1/32 inch.

H = Intersection of center lines to face of fitting; 90° elbows tees, crosses; ± 1/32 inch.

J = Intersection of center lines to bottom of socket/thread; 45° elbows; ± 1/32 inch

L = Overall length of fittings; ± 1/16 inch.

M = Outside diameter of socket/thread hub; ± 1/16 inch.

N = Socket bottom to socket bottom; couplings; ± 1/16 inch.

W = Height of cap; ± 1/16 inch

Typical Molded Dimension References

