

Part No: YS3AS8-012C

Filters & Strainers

Y-Strainers

Desc: 1-1/4 CPVC T/U Y STRAINER SOC FKM S8MESH

MSRP: 1214.19

Part Code: 104

Weight(lbs): 2.152

Weight(kg): 0.976

Weight(gm): 976

Size: 1-1/4"

Color: GRAY

Material: CPVC

Connection Socket - True Union

O-Ring FKM

Mesh Sieve # 8

Body Color Gray



A = 5-13/16

A1 = 8-5/8

B = 7-7/16

C = 9-15/16

D = 4-1/4

E = 2-13/16

Injection Molded Dimension References:

G = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses; $\pm 1/32$ inch.

H = Intersection of center lines to face of fitting; 90° elbows tees, crosses; $\pm 1/32$ inch.

J = Intersection of center lines to bottom of socket/thread; 45° elbows; $\pm 1/32$ inch

L = Overall length of fittings; $\pm 1/16$ inch.

M = Outside diameter of socket/thread hub; $\pm 1/16$ inch.

N = Socket bottom to socket bottom; couplings; $\pm 1/16$ inch.

W = Height of cap; $\pm 1/16$ inch

Typical Molded Dimension References

