

Part No: YS3AS8-030CL

Filters & Strainers

Y-Strainers

Desc: 3 PVC CL T/U Y STRAINER SOC FKM S8 MESH

MSRP: 1307.23

Part Code: 103

Weight(lbs): 10.468

Weight(kg): 4.748

Weight(gm): 4748

Size: 3"

Color: CLEAR

Material: PVC

Connection Socket - True Union

O-Ring FKM

Mesh Sieve # 8

Body Color Clear



A = 10-3/4

A1 = 16-1/6

B = 12-3/16

C = 16

D = 7-5/8

E = 5-1/8

Injection Molded Dimension References:

G = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses; $\pm 1/32$ inch.

H = Intersection of center lines to face of fitting; 90° elbows tees, crosses; $\pm 1/32$ inch.

J = Intersection of center lines to bottom of socket/thread; 45° elbows; $\pm 1/32$ inch

L = Overall length of fittings; $\pm 1/16$ inch.

M = Outside diameter of socket/thread hub; $\pm 1/16$ inch.

N = Socket bottom to socket bottom; couplings; $\pm 1/16$ inch.

W = Height of cap; $\pm 1/16$ inch

Typical Molded Dimension References

