

Part No: YS3BP8-012CL

Filters & Strainers

Y-Strainers

Desc: 1-1/4 PVC CL T/U Y STRAINER FPT FKM P8M

MSRP: 355.76

Part Code: 103

Weight(lbs): 1.962

Weight(kg): 0.89

Weight(gm): 890

Size: 1-1/4"

Color: CLEAR

Material: PVC

Connection Fipt - True Union

O-Ring FKM

Mesh Sieve # 8

Body Color Clear



D = 4-1/4

E = 2-13/16

A = 5-13/16

A1 = 8-5/8

B = 6-3/16

C = 10-1/8

Injection Molded Dimension References:

G = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses; $\pm 1/32$ inch.

H = Intersection of center lines to face of fitting; 90° elbows tees, crosses; $\pm 1/32$ inch.

J = Intersection of center lines to bottom of socket/thread; 45° elbows; $\pm 1/32$ inch

L = Overall length of fittings; $\pm 1/16$ inch.

M = Outside diameter of socket/thread hub; $\pm 1/16$ inch.

N = Socket bottom to socket bottom; couplings; $\pm 1/16$ inch.

W = Height of cap; $\pm 1/16$ inch

Typical Molded Dimension References

