

Part No: YS3BS8-007CL

Filters & Strainers

Y-Strainers

Desc: 3/4 PVC CL T/U Y STRAINER FPT FKM S8MESH

MSRP: 392.78

Part Code: 103

Weight(lbs): 0.871

Weight(kg): 0.395

Weight(gm): 395

Size: 3/4"

Color: CLEAR

Material: PVC

Connection Fipt - True Union

O-Ring FKM

Mesh Sieve # 8

Body Color Clear



A = 4-1/8

A1 = 6-3/16

B = 6-7/16

C = 7-7/8

D = 3

E = 2

Injection Molded Dimension References:

G = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses; $\pm 1/32$ inch.

H = Intersection of center lines to face of fitting; 90° elbows tees, crosses; $\pm 1/32$ inch.

J = Intersection of center lines to bottom of socket/thread; 45° elbows; $\pm 1/32$ inch

L = Overall length of fittings; $\pm 1/16$ inch.

M = Outside diameter of socket/thread hub; $\pm 1/16$ inch.

N = Socket bottom to socket bottom; couplings; $\pm 1/16$ inch.

W = Height of cap; $\pm 1/16$ inch

Typical Molded Dimension References

