

Part No: YS3BS8-020CL

Filters & Strainers

Y-Strainers

Desc: 2 PVC CL T/U Y STRAINER FPT FKM S8 MESH

MSRP: 797.32

Part Code: 103

Weight(lbs): 4.559

Weight(kg): 2.068

Weight(gm): 2068

Size: 2"

Color: CLEAR


Material: PVC

Connection Fipt - True Union

O-Ring FKM

Mesh Sieve # 8

Body Color Clear



A = 8-15/16

A1 = 12-7/16

B = 10-13/16

C = 12-13/16

D = 6-3/16

E = 3-1/2

Injection Molded Dimension References:

G = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses; $\pm 1/32$ inch.

H = Intersection of center lines to face of fitting; 90° elbows tees, crosses; $\pm 1/32$ inch.

J = Intersection of center lines to bottom of socket/thread; 45° elbows; $\pm 1/32$ inch

L = Overall length of fittings; $\pm 1/16$ inch.

M = Outside diameter of socket/thread hub; $\pm 1/16$ inch.

N = Socket bottom to socket bottom; couplings; $\pm 1/16$ inch.

W = Height of cap; $\pm 1/16$ inch

Typical Molded Dimension References

