

# Product data sheet

Specifications

SQUARE D



Manual Starter, integral horsepower, NEMA M0, 600 VAC, 3 pole, 5 HP at 380/575 VAC, three phase, no indicator, NEMA 1

2510MBG2

Product availability : Stock - Normally stocked in distribution facility

## Main

Product	Manual Starter
Type	M
NEMA Size	M-0

## Complementary

Control Unit	Push-button
Pilot Light	No indicator
Horsepower Rating	3 hp 200...230 V AC, 3 phase 5 hp 380...575 V AC, 3 phase
Voltage Rating	600 V AC
Number of Poles	3P
Starter Type	Non reversing
Electrical Connection	Pressure wire clamp
Overload Relay Type	Melting alloy
Number of Thermal Units Required	3
Wire Gauge	AWG 14...AWG 8 copper
Auxiliary Contacts	Without
Height	8.63 in (219.20 mm)
Width	5 in (127.00 mm)
Depth	4.13 in (104.90 mm)
Net Weight	4.14 lb(US) (1.88 kg)

## Environment

Certifications	CSA LR60905 class 3211 05 UL listed file E42243 CCN NLRV
NEMA Enclosure Rating	NEMA 1 painted sheet steel

## Ordering and shipping details

Category	21103-2510,2511,2512 M,T
----------	--------------------------

Discount Schedule	CP1
GTIN	785901792536
Returnability	Yes
Country of origin	MX

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4.60 in (11.684 cm)
Package 1 Width	5.70 in (14.478 cm)
Package 1 Length	9.10 in (23.114 cm)
Package 1 Weight	4.15 lb(US) (1.882 kg)
Unit Type of Package 2	PAL
Number of Units in Package 2	126
Package 2 Height	40.00 in (101.6 cm)
Package 2 Width	40.00 in (101.6 cm)
Package 2 Length	48.00 in (121.92 cm)
Package 2 Weight	535.00 lb(US) (242.672 kg)

## Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information.
RoHS exemption information	<a href="#">Yes</a>
PVC free	Yes

## Contractual warranty

Warranty	18 months
----------	-----------

