

Product data sheet

Specifications

SQUARE D



Manual Starter, integral horsepower, NEMA M1, 600 VAC, 3 pole, 10 HP at 380/575 VAC, three phase, no indicator, NEMA 12

2510MCA3

Product availability : Stock - Normally stocked in distribution facility

Price* : 509.69 USD

Main

| | |
|-----------|----------------|
| Product | Manual Starter |
| Type | M |
| NEMA Size | M-1 |

Complementary

| | |
|----------------------------------|-----------------------------------------------------------------|
| Control Unit | Push-button |
| Pilot Light | No indicator |
| Horsepower Rating | 7.5 hp 200...230 V AC, 3 phase 10 hp 380...575 V AC, 3 phase |
| Voltage Rating | 600 V AC |
| Number of Poles | 3P |
| Starter Type | Non reversing |
| Electrical Connection | Pressure wire clamp |
| Overload Relay Type | Melting alloy |
| Number of Thermal Units Required | 3 |
| Wire Gauge | AWG 14...AWG 8 copper |
| Auxiliary Contacts | Without |
| Height | 10.92 in (277.37 mm) |
| Width | 5.78 in (146.81 mm) |
| Depth | 5.76 in (146.30 mm) |

Environment

| | |
|-----------------------|-------------------------------------------------------------|
| Certifications | UL listed file E42243 CCN NLRV CSA LR60905 class 3211 05 |
| NEMA Enclosure Rating | NEMA 12 painted sheet steel |

Ordering and shipping details

| | |
|----------|--------------------------|
| Category | 21103-2510,2511,2512 M,T |
|----------|--------------------------|

* Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

| | |
|-------------------|--------------|
| Discount Schedule | CP1 |
| GTIN | 785901845317 |
| Returnability | Yes |
| Country of origin | MX |

Packing Units

| | |
|------------------------------|-----------------------|
| Unit Type of Package 1 | PCE |
| Number of Units in Package 1 | 1 |
| Package 1 Height | 6.10 in (15.5 cm) |
| Package 1 Width | 6.81 in (17.3 cm) |
| Package 1 Length | 11.42 in (29.0 cm) |
| Package 1 Weight | 6.99 lb(US) (3.17 kg) |

Offer Sustainability

| | |
|----------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| California proposition 65 | WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov |
| REACH Regulation | REACH Declaration |
| EU RoHS Directive | Compliant EU RoHS Declaration |
| Mercury free | Yes |
| China RoHS Regulation | China RoHS declaration Product out of China RoHS scope. Substance declaration for your information. |
| RoHS exemption information | Yes |
| PVC free | Yes |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

Recommended replacement(s)