

Product data sheet

Specifications

SQUARE D

 Green Premium™



Transformer, dry type, encapsulated, 5kVA, 1 phase, 240x480V primary, 120/240V secondary, 13B, 115C rise

5S1F

Product availability : Stock - Normally stocked in distribution facility

Main

Product or Component Type	Dry Sealed Transformer
Primary to Secondary Voltage	240 x 480 V 120/240 V
Full Capacity Taps	0

Complementary

Enclosure Code	13B
Phase	1 phase
Power Rating	5 kVA
Temperature rise	115 °C
Height	14.75 in (374.65 mm)
Width	9.75 in (247.65 mm)
Depth	11.75 in (298.45 mm)
Enclosure mounting	Wall mounted
Net Weight	115 lb(US) (52.16 kg) 114.91 lb(US) (52.12 kg)
Enclosure Material	Painted sheet steel

Environment

Enclosure Type	NEMA 3R
Insulation temperature	356 °F (180 °C)
Product Certifications	UL Listed CSA cULus

Ordering and shipping details

Category	16277-RESIN LVGP XFMR
Discount Schedule	PE2
GTIN	785901359425
Returnability	Yes
Country of origin	MX

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	14.75 in (37.465 cm)
Package 1 Width	9.75 in (24.765 cm)
Package 1 Length	11.75 in (29.845 cm)
Package 1 Weight	115.00 lb(US) (52.163 kg)
Unit Type of Package 2	PAL
Number of Units in Package 2	12
Package 2 Height	40.00 in (101.6 cm)
Package 2 Width	40.00 in (101.6 cm)
Package 2 Length	48.00 in (121.92 cm)
Package 2 Weight	1380.00 lb(US) (625.957 kg)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Phenyl glycidyl ether, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
PVC free	Yes

Contractual warranty

Warranty	18 months
-----------------	-----------

Recommended replacement(s)