

Product data sheet

Specifications

SQUARE D



Contactor, Definite Purpose, 40A,
2 pole, 208/240VAC coil at 60Hz,
220VAC coil at 50Hz, open

8910DP42V09

Product availability : Stock - Normally stocked in distribution facility

Price* : 83.75 USD

Main

Product or Component Type	Definite Purpose Contactor
Line Rated Current	40 A
Number of Poles	2P
Pole contact composition	2 NO
Range of Product	DP

Complementary

Maximum Horse Power Rating	2 hp 115 V AC, 1 phase 5 hp 230 V AC, 1 phase
Locked rotor rated current	240 A 277 V AC 200 A 460 V AC 160 A 575 V AC
[Ue] rated operational voltage	600 V AC
[Uc] control circuit voltage	208...240 V AC 60 Hz 220 V AC 50 Hz
Phase	1 phase
Electrical Connection	Quick connect terminals Box lugs

Environment

Product Certifications	UL Recognized CSA
------------------------	----------------------

Ordering and shipping details

Category	21358-8910 DP 42
Discount Schedule	CP1B
GTIN	785901024194
Returnability	Yes
Country of origin	CN

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1

* Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Package 1 Height	2.30 in (5.842 cm)
Package 1 Width	2.80 in (7.112 cm)
Package 1 Length	3.40 in (8.636 cm)
Package 1 Weight	10.24 oz (290.299 g)

Offer Sustainability

REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
RoHS exemption information	Yes

Contractual warranty

Warranty	18 months
----------	-----------

Recommended replacement(s)