

# Product data sheet

Specifications

**SQUARE D**



## Operating mechanism, flange mounted, variable depth, 30A, 600 V, no fuse, switch mechanism

9422TCN30

**Product availability : Stock - Normally stocked in distribution facility**

### Main

Range	9422T
Product	Disconnect Switch
Disconnect Type	Non-fusible disconnect switch

### Complementary

Mounting Type	Flange rod variable depth
Current Rating	30 A
Horsepower Rating	7.5 hp 200 V AC 7.5 hp 230 V AC 15 hp 460 V AC 20 hp 575 V AC 5 hp 250 V DC
Handle Type	Ordered separately

### Environment

Certifications	CSA UL Recognized
----------------	----------------------

### Ordering and shipping details

Category	21732-9422
Discount Schedule	CP1
GTIN	785901879749
Returnability	Yes
Country of origin	MX

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	7.20 in (18.3 cm)
Package 1 Width	11.10 in (28.2 cm)
Package 1 Length	16.10 in (40.9 cm)
Package 1 Weight	5.51 lb(US) (2.5 kg)

## Offer Sustainability

<b>California proposition 65</b>	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
<b>REACH Regulation</b>	<a href="#">REACH Declaration</a>
<b>REACH free of SVHC</b>	Yes
<b>EU RoHS Directive</b>	Compliant <a href="#">EU RoHS Declaration</a>
<b>Toxic heavy metal free</b>	Yes
<b>Mercury free</b>	Yes
<b>China RoHS Regulation</b>	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
<b>RoHS exemption information</b>	<a href="#">Yes</a>

## Contractual warranty

<b>Warranty</b>	18 months
-----------------	-----------

## Recommended replacement(s)