

Product data sheet

Specifications

SQUARE D

 Green Premium™



Load center accessory, QO/Homeline, ground bar kit, 7 terminals

PK7GTA

Product availability : Stock - Normally stocked in distribution facility

Main

Product line QO

Product type Bar

Complementary

Number of connectors 7

Wire size AWG 14...AWG 4 copper
AWG 12...AWG 4 aluminium

Provided equipment 2 screw

Bar length 2.87 in (73 mm)

Maximum length of segment 1.26 in (32 mm)

Device mounting Direct mounting back of enclosure

Height 0.437 in (11.10 mm)

Depth 0.312 in (7.92 mm)

Tightening torque 30 lb.in
Mounting screw 30 lb.in
20 lb.in, AWG 14...AWG 10, copper
20 lb.in, AWG 12...AWG 10, aluminium
35 lb.in, AWG 6...AWG 4
25 lb.in, AWG 8
25 lb.in, AWG 14...AWG 12, copper
25 lb.in, AWG 12...AWG 10, aluminium

Ordering and shipping details

Category 00102-QO LC ACCESSORIES

Discount Schedule DE3A

GTIN 785901026372

Returnability Yes

Country of origin US

Packing Units

Unit Type of Package 1 PCE

Number of Units in Package 1 1

Package 1 Height 0.40 in (1.016 cm)

Package 1 Width 1.20 in (3.048 cm)

Package 1 Length	5.00 in (12.7 cm)
Package 1 Weight	1.60 oz (45.359 g)
Unit Type of Package 2	PAL
Number of Units in Package 2	2160
Package 2 Height	26.50 in (67.31 cm)
Package 2 Width	40.00 in (101.6 cm)
Package 2 Length	48.00 in (121.92 cm)
Package 2 Weight	260.00 lb(US) (117.934 kg)


Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: Cancer and Reproductive Harm - www.P65Warnings.ca.gov
REACh Regulation	REACh Declaration
REACh free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
-----------------	-----------

Dimensions



Recommended replacement(s)