

# Product data sheet

## Specifications



Busway, I-Line, Fusible plug in unit,  
100A, 600V, 3 pole, Class H fuse

PQ3610G

**Product availability : Stock - Normally stocked in distribution facility**

Price\* : 1,512.00 USD

## Main

## Product or Component Type      Section

## Complementary

|                                       |          |
|---------------------------------------|----------|
| <b>Fixing Mode</b>                    | Plug-in  |
| <b>[Ue] rated operational voltage</b> | 600 V AC |
| <b>[Ie] rated operational current</b> | 100 A    |
| <b>Number of poles</b>                | 3        |
| <b>Busbar description</b>             | Ground   |
| <b>Fuse type</b>                      | H        |

## Environment

## Product Certifications

## Ordering and shipping details

|                          |                                  |
|--------------------------|----------------------------------|
| <b>Category</b>          | 20177-PQ 30/60/100 FUSIBLE PLUGS |
| <b>Discount Schedule</b> | PE7                              |
| <b>GTIN</b>              | 785901263920                     |
| <b>Returnability</b>     | Yes                              |
| <b>Country of origin</b> | MX                               |

## Packing Units

|                                     |                         |
|-------------------------------------|-------------------------|
| <b>Unit Type of Package 1</b>       | PCE                     |
| <b>Number of Units in Package 1</b> | 1                       |
| <b>Package 1 Height</b>             | 10.90 in (27.686 cm)    |
| <b>Package 1 Width</b>              | 13.20 in (33.528 cm)    |
| <b>Package 1 Length</b>             | 22.80 in (57.912 cm)    |
| <b>Package 1 Weight</b>             | 17.51 lb(US) (7.942 kg) |
| <b>Unit Type of Package 2</b>       | PAL                     |
| <b>Number of Units in Package 2</b> | 32                      |

\* Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

|                         |                            |
|-------------------------|----------------------------|
| <b>Package 2 Height</b> | 40.00 in (101.6 cm)        |
| <b>Package 2 Width</b>  | 40.00 in (101.6 cm)        |
| <b>Package 2 Length</b> | 48.00 in (121.92 cm)       |
| <b>Package 2 Weight</b> | 561.00 lb(US) (254.465 kg) |

## Offer Sustainability

|                                   |   |
|-----------------------------------|---|
| <b>Sustainable offer status</b>   | Green Premium product   |
| <b>California proposition 65</b>  | WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Bisphenol A (BPA), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a> |
| <b>REACH Regulation</b>           | <a href="#">REACH Declaration</a>   |
| <b>EU RoHS Directive</b>          | Compliant<br><a href="#">EU RoHS Declaration</a>  |
| <b>Mercury free</b>               | Yes   |
| <b>China RoHS Regulation</b>      | <a href="#">China RoHS declaration</a><br>Product out of China RoHS scope. Substance declaration for your information.  |
| <b>RoHS exemption information</b> | <a href="#">Yes</a>   |
| <b>Environmental Disclosure</b>   | <a href="#">Product Environmental Profile</a>   |
| <b>Circularity Profile</b>        | <a href="#">End of Life Information</a>   |
| <b>PVC free</b>                   | Yes   |

## Contractual warranty

|                 |           |
|-----------------|-----------|
| <b>Warranty</b> | 18 months |
|-----------------|-----------|

## Recommended replacement(s)