

Product data sheet

Specifications

SQUARE D

Green Premium™



Mini circuit breaker, QO, 150A, 3 pole, 120/240VAC, 22kA, bolt on mount

QOB3150VH

Product availability : Stock - Normally stocked in distribution facility

Main

Product	Miniature circuit-breaker
Range	QO
Current Rating	150 A
Voltage Rating	120/240 V AC 240 V AC 120 V AC
Mounting Type	Bolt-on
Number of Poles	3P
Circuit Breaker Type	Standard
Ratings	Not rated
Electrical Connection	Box lugs

Complementary

Interrupt Rating	22 kA 120/240 V AC 50/60 Hz 22 kA 240 V AC 50/60 Hz 22 kA 120 V AC 50/60 Hz
Number of Panel Spaces	6
Wire Size	AWG 4...300 kcmil copper or aluminium
Tightening Torque	40.71 lbf.in (4.6 N.m)
Height	5.71 in (145 mm)
Width	4.49 in (114 mm)
Depth	4.88 in (124 mm)
Net Weight	0.55 lb(US) (0.249 kg)

Environment

Certifications	UL Listed CSA
Ambient Rating	104 °F (40 °C)

Ordering and shipping details

Category	00015-QOB CIRCUIT BREAKERS
Discount Schedule	DE2

GTIN	785901065517
Returnability	Yes
Country of origin	MX

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4.30 in (10.922 cm)
Package 1 Width	5.00 in (12.7 cm)
Package 1 Length	6.70 in (17.018 cm)
Package 1 Weight	3.94 lb(US) (1.787 kg)
Unit Type of Package 2	PAL
Number of Units in Package 2	558
Package 2 Height	40.00 in (101.6 cm)
Package 2 Width	40.00 in (101.6 cm)
Package 2 Length	48.00 in (121.92 cm)
Package 2 Weight	2199.00 lb(US) (997.449 kg)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Cadmium and cadmium compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
RoHS exemption information	Yes
Halogen content performance	Halogen free product

Contractual warranty

Warranty	18 months
----------	-----------

Recommended replacement(s)