



Actual

Catalog Number: RB14-110F
Product ID: 7TAI029700R0025
UPC Number: 78621080686
EAN Number: 05414363158318
Status: A

Nylon Insulated Female Disconnect, Length .75 Inches, Width 0.15, Maximum Insulation .135, Tab Size .110x.032, Wire Range #16-#14 AWG, Color Blue, Copper, Tin Plated, 100 Pack

- Alternate Package Qty: RB10SK

North American Specifications (UNSPSC)

UNSPSC	39121447 Wire terminal disconnect
IGCC	4667 Wire terminal disconnect
Brand Name	Sta-Kon
Type	Disconnects
Material	Brass
Finish	Tin Plated
Color	Blue
Insulation	Nylon/Polyamide

European Specifications (ETIM)

ETIM	EC000516 Round or flat plug/receptacle
Insulation	Partially Insulated
Colour insulation	Blue
Material insulation	PA
Material	Copper

Packaging

Inner Quantity	100
Inner Dimensions (inches)	2.09x1.1x3
Outer Quantity	500
Outer Dimensions (inches)	10.4x7.3x9
Weight Uom	1.88 lbs. per 1000

Documents / Support Tools

Technical Drawing / Data Sheet US	Available on Website
-----------------------------------	----------------------