

Enclosures **CF Series**

Polycarbonate Enclosure 4 x 3 x 2 Inches CF Series Slim with Opaque Lift Off Cover



**Catalog
Number**

CFPC432

UPC

785928564581


DESCRIPTION

4H x 3W x 2D Inches Polycarbonate CF Series Slim Enclosure with Opaque Lift Off Cover is ideal for compact or portable control or simply as a small junction box. This stream lines series features unobstructed sidewalls, captive cover screws and a full range of sizes.

APPLICATION

- For use in many MRO and OEM applications
- Slim design allows easy installation of pushbuttons and switches in machine control applications with tight or dense space requirements
- Used in compact or portable control systems or for use as an Operator Interface Enclosure in both indoor and outdoor environments
- Used as general Junction Enclosures or termination point enclosures in an electrical system
- Used indoors or outdoors

FEATURES



- Memory retaining continuous polyurethane gasket
- Corrosion resistant polycarbonate
- Submersible; non corrosive; environmental design
- High Impact Resistance

General Information

Color	Gray
Cover Type	Opaque
Mounting Type	Wall Mount
Material	Polycarbonate
Cover Screw Size	Custom
Cover Screw Recommended Torque	16-20 in-lbs
Cover Screw Material	Polycarbonate
Installation Mounting Torque	25-30 in-lbs Max
Metal Inserts	
Gasket Material	Poured In Place (PIP) Polyurethane Seamless
Country of Origin	USA

DIMENSIONS

Height (in)	4
Width (in)	3
Depth (in)	2
Height (mm)	101.6
Width (mm)	76.2
Depth (mm)	50.8
Usable Depth (in)	2.51
Usable Depth (mm)	64

STANDARDS

NEMA 10250; UL 50; UL 50e; UL508A	cULus Listed File #E64358
CSA Std. C22.2	cULus Listed File #E64358
Type	1; 3R; 4; 4X; 6P; 12
IEC 60529; UL Listed #E362920	IP66; IP68
Temperature Range °F	-40°F to +248°F
Temperature Range °C	-40°C to +120°C
Flammability Rating	UL94-5VA
Outdoor Exposure UL746c	(f1) Rated
CE	Certified