

Catalog Number: 51-20R
Product ID: 7TAA001480R0002
UPC Number: 78599105715
Status: Active

Gangable Switch Box, 10 Cubic Inches, 3 Inches Long x 2 Inches Wide x 2 Inches Deep, 1/2 Inch Knockouts, Galvanized Steel, Two Nail Holes in Sides, Furnished with Plaster Ears, pack of 20, for Retail

North American Specifications (UNSPSC)

UNSPSC	39121306 Switch box
IGCC	4430 Switch box
Brand Name	Steel City
Type	Switch Boxes
Application	For use with conduit
Standard	UL E2969
Material	Steel
Size	3 Inches Height x 2 Inches Width x 2-1/4 inches depth
Color	Silver
Cubic Capacity	10 Cubic Inches
Knockouts	Yes
Number Of Outlet	1

European Specifications (ETIM)

ETIM	EC000080 Surface mounted housing for flush mounted switching device
Assembly arrangement	Surface mounted housing
Mounting direction	Vertical
Material	Metal
Colour	Silver
Transparent	N
Width of device	50.8mm

Packaging

Outer Quantity	20
Outer Dimensions (inches)	13.12x7.25x4.75
Weight Uom	47 lbs. per 100

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email:techsupport@tnb.com