



Actual

Catalog Number: 54151NV-25R
Product ID: 7TBA001370R0051
UPC Number: 78599108261
Status: Active

Octagon Box, 15.8 Cubic Inches, 4 Inch Diameter x 1-1/2 Inches Deep, 1/2 Inch Knockouts, Pre-Galvanized Steel, Drawn Construction, with Non-Metallic Cable Clamps (C-5) and V Bracket, For use with Non-Metallic Sheathed Cable, pack of 25, for Retail

North American Specifications (UNSPSC)

UNSPSC	39121316 Ceiling box
IGCC	4449 Box/housing for built-in mounting in the wall/ceiling
Brand Name	Steel City
Type	Octagonal Boxes
Application	For use with non-metallic sheathed cable
Standard	UL E2969
Number Of Outlet	1
Material	Steel
Size	4 Inches Diameter x 1/2 Inch depth
Color	Silver
Cubic Capacity	15.8 Cubic Inches
Knockouts	Yes
Construction	Drawn

European Specifications (ETIM)

ETIM	EC002600 Box/housing for surface mounting on the wall/ceiling
Shape	Octagonal
Mounting method	Wall-/ceiling mounting
Depth	38.1mm
Diameter	101.6mm
Material	Steel
Weatherproof	N

Packaging

Outer Quantity	25
Outer Dimensions (inches)	20.5x8.75x9
Weight Uom	67.5 lbs. per 100

For further technical assistance, please contact us...

Thomas & Betts - USA
 8155 T&B Blvd.
 Memphis, TN 38125
www.tnb.com

T&B Technical Support
 MS 3B-50
 8155 T&B Blvd.
 Memphis, TN 38125

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com