



Actual

**Catalog Number:** 541711234-25R  
**Product ID:** 7TAA001350R0044  
**UPC Number:** 78599105996  
**Status:** Active

Octagon Box, 22.5 Cubic Inches, 4 Inch Diameter x 2-1/8 Inches Deep, 12/ Inch and 3/4 Inch Knockouts, Pre-Galvanized Steel, Drawn Construction, For use with Conduit, pack of 25, for Retail

### North American Specifications (UNSPSC)

UNSPSC	39121316 Ceiling box
IGCC	4449 Box/housing for built-in mounting in the wall/ceiling
Brand Name	Steel City
Type	Octagonal Boxes
Application	For use with conduit
Standard	UL E2969
Number Of Outlet	1
Material	Steel
Size	4 Inches Diameter x 2-1/8 Inches depth
Color	Silver
Cubic Capacity	22.5 Cubic Inches
Knockouts	Yes
Construction	Drawn

### European Specifications (ETIM)

ETIM	EC002600 Box/housing for surface mounting on the wall/ceiling
Shape	Octagonal
Mounting method	Wall-/ceiling mounting
Depth	53.975mm
Diameter	101.6mm
Material	Steel
Weatherproof	N

### Packaging

Outer Quantity	25
Outer Dimensions (inches)	18.75x8.25x7.5
Weight Uom	59.5 lbs. per 100

For further technical assistance, please contact us...

Thomas & Betts - USA  
 8155 T&B Blvd.  
 Memphis, TN 38125  
[www.tnb.com](http://www.tnb.com)

T&B Technical Support  
 MS 3B-50  
 8155 T&B Blvd.  
 Memphis, TN 38125

Hours: 7AM - 6PM CDT  
 Monday-Friday  
 Phone: (888) 862-3289  
 Fax: (901) 252-1321  
 Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)