



Actual

Catalog Number: 54171CFB-BHL-OW
Product ID: 7TAA001800R0000
UPC Number: 78599104122
Status: Active

Octagon Ceiling Fan Support Box, 22.5 Cubic Inches, 4 Inch Diameter x 2-1/8 Inches Deep, 1/2 Inch Knockouts, Pre-Galvanized Steel, Drawn Construction, Non-Metallic Cable Clamp (C-5) and Old Work Bar Hanger with 16 Inch to 24 Inch Length, For use with Non-Metallic Sheathed Cable

North American Specifications (UNSPSC)

UNSPSC	39121316 Ceiling box
IGCC	4449 Box/housing for built-in mounting in the wall/ceiling
Brand Name	Steel City
Type	Octagonal Boxes
Special Features	Expandable for joists spaced from 16 to 24 inches
Application	For use with non-metallic sheathed cable
Standard	UL E2969
Number Of Outlet	1
Material	Steel
Size	4 Inches Diameter x 2-1/8 Inches depth
Color	Silver
Cubic Capacity	22.5 Cubic Inches
Knockouts	Yes
Construction	Drawn

European Specifications (ETIM)

ETIM	EC001796 Junction box for ceiling luminaire
Outlet diameter	101.6mm

Packaging

Inner Quantity	1
Inner Dimensions (inches)	4.25x4.25x2.69
Outer Quantity	10
Outer Dimensions (inches)	13.5x8.75x4.75
Weight Uom	2.62 lbs. Each

Documents / Support Tools

Instruction Sheet 1	ta04760-tb2
---------------------	-------------

For further technical assistance, please contact us...

Thomas & Betts - USA
 8155 T&B Blvd.
 Memphis, TN 38125
 www.tnb.com

T&B Technical Support
 MS 3B-50
 8155 T&B Blvd.
 Memphis, TN 38125

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com