



Actual

**Catalog Number:** 5835112-25R  
**Product ID:** 7TAA001450R0035  
**UPC Number:** 78599108252  
**Status:** Active

One Gang Utility Box, 10.3 Cubic Inches, 4 Inches Long x 2-1/8 Inches Wide x 1-1/2 Inches Deep, 1/2 Inch Knockouts, Pre-Galvanized Steel, Drawn Construction, For use with Conduit, pack of 25, for Retail

### North American Specifications (UNSPSC)

UNSPSC	39121310 Utility boxes
IGCC	4440 Utility boxes
Brand Name	Steel City
Type	Utility Boxes
Special Features	Factory provided raised ground screw location.
Application	For use with conduit
Standard	UL E2969
Number Of Outlet	1
Material	Steel
Size	4 Inches Length x 2-1/8 Inches Width x 1-1/2 Inches Depth
Color	Silver
Construction	Drawn
Cubic Capacity	10.3 Cubic Inches
Knockouts	Yes

### European Specifications (ETIM)

ETIM	EC000080 Surface mounted housing for flush mounted switching device
Assembly arrangement	Surface mounted housing
Mounting direction	Vertical
Material	Metal
Colour	Silver
Transparent	N
Width of device	53.975mm

### Packaging

Outer Quantity	25
Outer Dimensions (inches)	11.3x8.5x5
Weight Uom	42 lbs. per 100

For further technical assistance, please contact us...

Thomas & Betts - USA  
 8155 T&B Blvd.  
 Memphis, TN 38125  
[www.tnb.com](http://www.tnb.com)

T&B Technical Support  
 MS 3B-50  
 8155 T&B Blvd.  
 Memphis, TN 38125

Hours: 7AM - 6PM CDT  
 Monday-Friday  
 Phone: (888) 862-3289  
 Fax: (901) 252-1321  
 Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)