



Actual

Catalog Number: 5836112-50R
Product ID: 7TAA001450R0034
UPC Number: 78599108247
Status: Active

One Gang Utility Box, 13.0 Cubic Inches, 4 Inches Long x 2-1/8 Inches Wide x 1-7/8 Inches Deep, 1/2 Inch Knockouts, Pre-Galvanized Steel, Drawn Construction, For use with Conduit, pack of 50, for Retail

North American Specifications (UNSPSC)

UNSPSC	39121310 Utility boxes
IGCC	4440 Utility boxes
Brand Name	Steel City
Type	Utility Boxes
Special Features	Factory provided raised ground screw location.
Application	For use with conduit
Standard	UL E2969
Number Of Outlet	1
Material	Steel
Size	4 Inches Length x 2-1/8 Inches Width x 1-7/8 Inches Depth
Color	Silver
Construction	Drawn
Cubic Capacity	13 Cubic Inches
Knockouts	Yes

European Specifications (ETIM)

ETIM	EC000080 Surface mounted housing for flush mounted switching device
Assembly arrangement	Surface mounted housing
Mounting direction	Vertical
Material	Metal
Colour	Silver
Transparent	N
Width of device	53.975mm

Packaging

Outer Quantity	50
Outer Dimensions (inches)	11.3x8.3x9.5
Weight Uom	50 lbs. per 100

For further technical assistance, please contact us...

Thomas & Betts - USA
 8155 T&B Blvd.
 Memphis, TN 38125
www.tnb.com

T&B Technical Support
 MS 3B-50
 8155 T&B Blvd.
 Memphis, TN 38125

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com