



Actual

Catalog Number: 6010ADW-25R
Product ID: 7TBA001350R0062
UPC Number: 78599108256
Status: Active

Adjustable Bar Hanger, Bar Length 14-1/2 Inches to 26-1/2 Inches, Depth of End Plate 13/16 Inches, Stud, Pre-Galvanized Steel, Maximum Load Rating 50 Pounds, For 3/8 Inches, 1/2 Inches, and 5/8 Inches Wall Board and Plaster, for Retail

North American Specifications (UNSPSC)

UNSPSC	31162306 Mounting hangers
IGCC	2981 Mounting hangers
Brand Name	Steel City
Type	Bar Hangers
Application	For 3/8 Inches, 1/2 Inches, and 5/8 Inches Wall Board and Plaster
Material	Steel
Size	14-1/2 Inches to 26-1/2 Inches
Color	Silver
Load Capacity	50 Pounds
Included	Stud
Installation	Claws provide temporary support for proper positioning until permanently installed.

European Specifications (ETIM)

ETIM	EC002328 Accessories for junction boxes/junction cases for mounting in the wall
Suitable for built-in installation box	Y
Type of accessory	Other

Packaging

Outer Quantity	25
Outer Dimensions (inches)	19.25x8x5.5
Weight Uom	64 lbs. per 100

For further technical assistance, please contact us...

Thomas & Betts - USA
 8155 T&B Blvd.
 Memphis, TN 38125
 www.tnb.com

T&B Technical Support
 MS 3B-50
 8155 T&B Blvd.
 Memphis, TN 38125

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com