



Representative

**Catalog Number:** 642 3/4-1 1/4AL  
**Product ID:** 7TAA003980R0018  
**UPC Number:** 78599101613  
**Status:** Active

Two Gang Flush Service Floor Box, 74 Cubic Inches, Length 5-1/2 Inches, Width 7 Inches, Depth 3-5/8 Inches, 3/4 Inch and 1 Inch Conduit Hubs, Aluminum

### North American Specifications (UNSPSC)

UNSPSC	39121307 Floor boxes
IGCC	4432 Floor boxes
Brand Name	Steel City
Type	Two Gang Flush Service Floor Box
Special Features	Fully adjustable
Application	Ideal for the modern office with workstations that have power, communications and data equipment
Material	Aluminum
Cubic Capacity	74 Cubic Inches

### European Specifications (ETIM)

ETIM	EC000024 Installation box for underfloor-installation
Cover model	Rectangular
Suitable for wet cleaning	N
Suitable for hollow floor	Y
Material	Aluminium
With opening carpeting	N
Min. built-in depth	101.6mm
Colour	Other
Length external dimension	139.7mm
Width outside dimension	177.8mm

### Packaging

Outer Quantity	2
Outer Dimensions (inches)	7.5x7.5x6.62
Weight Uom	1010 lbs. per 100

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
 8155 T&B Blvd.  
 Memphis, TN 38125  
[www.tnb.com](http://www.tnb.com)

T&B Technical Support  
 MS 3B-50  
 8155 T&B Blvd.  
 Memphis, TN 38125

Hours: 7AM - 6PM CDT  
 Monday-Friday  
 Phone: (888) 862-3289  
 Fax: (901) 252-1321  
 Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)