



Family

Catalog Number: A257-20R
Product ID: 7TBA001460R0033
UPC Number: 78599109408
Status: Active

Non-Gangable Switch Box, 12.5 Cubic Inches, 3 Inches Long x 2 Inches Wide x 2-1/2 Inches Deep, 1/2 Inch Knockouts, Pre-Galvanized Steel, with Non-Metallic Cable Clamps (C-5) and Nails Slanted for Easy Drive-In, For Non-Metallic Sheathed Cable. Carton of 20.

North American Specifications (UNSPSC)

UNSPSC	39121306 Switch box
IGCC	4430 Switch box
Brand Name	Steel City
Type	Switch Boxes
Application	For use with non-metallic sheathed cable
Material	Steel
Size	3 Inches Height x 2 Inches Width x 2-1/2 inches depth
Color	Silver
Cubic Capacity	12.5 Cubic Inches
Knockouts	Yes
Number Of Outlet	1

European Specifications (ETIM)

ETIM	EC000080 Surface mounted housing for flush mounted switching device
Assembly arrangement	Surface mounted housing
Mounting direction	Vertical
Material	Metal
Colour	Silver
Transparent	N
Width of device	50.8mm

Packaging

Outer Quantity	20
Outer Dimensions (inches)	11.31x8.31x8.37
Weight Uom	64 lbs. per 100

For further technical assistance, please contact us...

Thomas & Betts - USA
 8155 T&B Blvd.
 Memphis, TN 38125
www.tnb.com

T&B Technical Support
 MS 3B-50
 8155 T&B Blvd.
 Memphis, TN 38125

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com