



Representative

Catalog Number: AFM4BLK2D50
Product ID: 7TAA003980R0078
UPC Number: 78599102825
Status: Active

Three Compartment Raised Access Floor Module, 150 Cubic Inches, Floor Cut Out Length 7-15/16 Inches, Width 7-15/16 Inches, Cover Size Length 7-5/8 Inches, Width 7-5/8 Inches, Depth 4 Inches, Galvanized Steel with Black Cover and 2 20A Duplexes and 50 Foot Whip

North American Specifications (UNSPSC)

UNSPSC	39121309 Specialty electrical boxes
IGCC	4439 Specialty electrical boxes
Brand Name	Steel City
Type	Three Compartment Raised Access Floor Module
Special Features	Easy to install and designed to blend with any decor
Application	For use with most types of raised floors including ridged or waffled floor panels, carpet or tile
Material	Steel
Color	Black
Cubic Capacity	150 Cubic Inches

European Specifications (ETIM)

ETIM	EC000024 Installation box for underfloor-installation
Cover model	Square
Suitable for wet cleaning	N
Suitable for hollow floor	Y
Material	Other
With opening carpeting	N
Min. built-in depth	142.875mm
Colour	Other
Length external dimension	201.5998mm
Width outside dimension	201.5998mm
Length built-in dimension	193.675mm
Width built-in dimension	193.675mm

Packaging

Outer Quantity	1
Outer Dimensions (inches)	18x18x12
Weight Uom	15 lbs. Each

For further technical assistance, please contact us...

Thomas & Betts - USA
 8155 T&B Blvd.
 Memphis, TN 38125
 www.tnb.com

T&B Technical Support
 MS 3B-50
 8155 T&B Blvd.
 Memphis, TN 38125

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email:techsupport@tnb.com