



Family

**Catalog Number:** CW 1/2 WOBC  
**Product ID:** 7TBA001500R0047  
**UPC Number:** 78599102462  
**Status:** Active

Gangable Switch Box, 14 Cubic Inches, 3 Inches Long x 2 Inches Wide x 2-3/4 Inches Deep, 1/2 Inch Knockouts, Pre-Galvanized Steel, Ears Flush for Old Work, without Bar Code, For use with Conduit

### North American Specifications (UNSPSC)

UNSPSC	39121306 Switch box
IGCC	4430 Switch box
Brand Name	Steel City
Type	Switch Boxes
Application	For use with conduit
Material	Steel
Size	3 Inches Height x 2 Inches Width x 2-3/4 inches depth
Color	Silver
Cubic Capacity	14 Cubic Inches
Knockouts	Yes
Number Of Outlet	1

### European Specifications (ETIM)

ETIM	EC000080 Surface mounted housing for flush mounted switching device
Assembly arrangement	Surface mounted housing
Mounting direction	Vertical
Material	Metal
Colour	Silver
Transparent	N
Width of device	50.8mm

### Packaging

Outer Quantity	50
Outer Dimensions (inches)	19.5x11.5x6.2
Weight Uom	57.5 lbs. per 100

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
 8155 T&B Blvd.  
 Memphis, TN 38125  
[www.tnb.com](http://www.tnb.com)

T&B Technical Support  
 MS 3B-50  
 8155 T&B Blvd.  
 Memphis, TN 38125

Hours: 7AM - 6PM CDT  
 Monday-Friday  
 Phone: (888) 862-3289  
 Fax: (901) 252-1321  
 Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)