



Actual

Catalog Number: L6912-2
Product ID: 7TAA010090R0007
UPC Number: 78599118470
Status: Active

1/2 Inch Liquidtight Strain Relief Cord Connector-Straight. Body Material-Die Cast Zinc. Gland material-Steel. Bushing-Neoprene. Cord range-.250-.375

North American Specifications (UNSPSC)

UNSPSC	39121420 Liquid tight connectors
IGCC	4585 Liquid tight connectors
Brand Name	Steel City
Type	Liquidtight Strain Relief Cord Connector
Size	1/2 Inch
Material	Zinc Die Cast
Insulation	None

European Specifications (ETIM)

ETIM	EC001180 Screw connection for protective metallic hose
Nominal size in inch	1/2 inch
Model	Straight
Revolving thread	N
One-piece	Y
Material housing	Zinc die-cast
Surface protection	Untreated
Approved in combination with protective conduit DIN EN 61386-23	N
Approved in combination with protective conduit FI	N

Packaging

Inner Quantity	10
Inner Dimensions (inches)	12.25x3.125x5
Outer Quantity	100
Outer Dimensions (inches)	16x12.75x10.5
Weight Uom	17 lbs. per 100

For further technical assistance, please contact us...

Thomas & Betts - USA
 8155 T&B Blvd.
 Memphis, TN 38125
www.tnb.com

T&B Technical Support
 MS 3B-50
 8155 T&B Blvd.
 Memphis, TN 38125

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com