

Catalog Number: LN101-10
Product ID: 7TAA117190R0007
UPC Number: 78599118349
Status: Active

1/2 Inch Locknut, Rigid/IMC Steel-Zinc Plated 10/bg

North American Specifications (UNSPSC)

UNSPSC	31161716 Locknuts
IGCC	2849 Locknuts
Brand Name	Steel City
Type	Locknut for Conduit Fitting
Application	For Use with Rigid/IMC Conduit
Material of Construction	Steel
Finish	Zinc Plated
Size	1/2 Inch

European Specifications (ETIM)

ETIM	EC000940 Locknut for cable screw gland
Thread type	NPT
Nominal thread size inch/gas pipe thread	1/2 inch
Material	Metal
Material quality	Steel
Surface protection	Other
Colour	Natural colour

Packaging

Inner Quantity	25
Inner Dimensions (inches)	11.2x6.5x5.2
Outer Quantity	250
Outer Dimensions (inches)	22.1x17.5x14.5
Weight Uom	13.13 lbs. per 100

Documents / Support Tools

Technical Data Sheet US	Available on Website
-------------------------	----------------------

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email:techsupport@tnb.com