

**Catalog Number:** SB-236-V  
**Product ID:** 7TAA040980R0126  
**UPC Number:** 78599101785  
**Status:** Active

Two-Gang Outlet Box, Volume 36 Cubic Inches, Length 3-9/16 Inches, Width 4 Inches, Depth 3-3/16 Inches, Color Black, Material Thermoplastic, Mounting Means 3/8 Inch Offset Bracket, with Molded V-Clamps

**North American Specifications (UNSPSC)**

UNSPSC	39121308 Outlet box
IGCC	4433 Outlet box
Brand Name	Carlon
Type	Two-Gang Outlet Box
Standard	UL E11461
Material	Thermoplastic
Color	Black
Mounting	3/8 Inch Offset Bracket
Cubic Capacity	36 Cubic Inches

**European Specifications (ETIM)**

ETIM	EC002601 Box/housing for built-in mounting in the wall/ceiling
Mounting method	Other
Shape	Rectangular
Construction type	Device connection box (round/square)
Equipped with	Mounting plate
Length	90.4748mm
Width	101.6mm
Depth	80.9498-80.9498mm
Mounting switching equipment	Screwing
With screws	N
Pipe locking	N
Pipe locking optional	N
Inlet from the rear	N
Material	Plastic
Colour	Black
Cover	None
Cover attachment	Not applicable
Sealable	N

**Packaging**

Outer Quantity	50
Outer Dimensions (inches)	25.75x18.5x8
Weight Uom	48 lbs. per 100

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
8155 T&B Blvd.  
Memphis, TN 38125  
www.tnb.com

T&B Technical Support  
MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email:techsupport@tnb.com