



Actual

Catalog Number: SB2-236-V
Product ID: 7TAA040980R0127
UPC Number: 78599101786
Status: Active

Two-Gang Outlet Box, Volume 36 Cubic Inches, Length 3-9/16 Inches, Width 4 Inches, Depth 3-3/16 Inches, Color Black, Material Thermoplastic, Mounting Means Two 3/8 Inch Offset Brackets, with Molded V-Clamps

North American Specifications (UNSPSC)

UNSPSC	39121308 Outlet box
IGCC	4433 Outlet box
Brand Name	Carlon
Type	Two-Gang Outlet Box
Material	Thermoplastic
Color	Black
Mounting	3/8 Inch Offset Bracket
Cubic Capacity	36 Cubic Inches

European Specifications (ETIM)

ETIM	EC002601 Box/housing for built-in mounting in the wall/ceiling
Mounting method	Other
Shape	Rectangular
Construction type	Device connection box (round/square)
Equipped with	Mounting plate
Length	90.4748mm
Width	101.6mm
Depth	80.9498-80.9498mm
Mounting switching equipment	Screwing
With screws	N
Pipe locking	N
Pipe locking optional	N
Inlet from the rear	N
Material	Plastic
Colour	Black
Cover	None
Cover attachment	Not applicable
Sealable	N

Packaging

Outer Quantity	20
Outer Dimensions (inches)	19.25x11.5x9.31
Weight Uom	73.75 lbs. per 100

For further technical assistance, please contact us...

Thomas & Betts - USA
 8155 T&B Blvd.
 Memphis, TN 38125
www.tnb.com

T&B Technical Support
 MS 3B-50
 8155 T&B Blvd.
 Memphis, TN 38125

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com