



Representative

Catalog Number: SP 642 3/4 1 AL
Product ID: 7TAA003980R0345
UPC Number: 78599102862
Status: Active

Two Gang Flush Service Floor Box, 74 Cubic Inches, Length 4-1/2 Inches, Width 3 Inches, 3/4 Inch and 1 Inch Conduit Hubs, Cast Iron with Aluminum Trim, Watertight, Adjustable, Concrete Applications Only

North American Specifications (UNSPSC)

UNSPSC	39121307 Floor boxes
IGCC	4432 Floor boxes
Brand Name	Steel City
Type	Two Gang Flush Service Floor Box
Special Features	Fully adjustable
Application	Ideal for the modern office with workstations that have power, communications and data equipment
Material	Cast Iron
Cubic Capacity	74 Cubic Inches

European Specifications (ETIM)

ETIM	EC000024 Installation box for underfloor-installation
Cover model	Rectangular
Suitable for wet cleaning	N
Suitable for hollow floor	Y
Material	Aluminium
With opening carpeting	N
Min. built-in depth	71.4248mm
Colour	Other
Length external dimension	114.3mm
Width outside dimension	244.475mm

Packaging

Outer Quantity	2
Weight Uom	740 lbs. per 100

For further technical assistance, please contact us...

Thomas & Betts - USA
 8155 T&B Blvd.
 Memphis, TN 38125
www.tnb.com

T&B Technical Support
 MS 3B-50
 8155 T&B Blvd.
 Memphis, TN 38125

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com