



Representative

Catalog Number: SP642 11/4AL
Product ID: 7TAA003050R0013
UPC Number: 78599104775
Status: Active

Two Gang Flush Service Floor Box, 74 Cubic Inches, Length 4-1/2 Inches, Width 3 Inches, 1-1/4 Inch Conduit Hubs, Cast Iron with Aluminum Trim, For Power, Communications, and Data

- Fully adjustable
- Cast iron watertight body and painted silver enamel inside and out for additional corrosion resistance
- Interior and exterior leveling screws permit adjustment to finished floor with removable partitions for large capacity requirements on 2, 3 and 4 gang.
- Shipped complete with expendable cap to prevent ingress of concrete during pour.

Header

3D Model Available on Website

North American Specifications (UNSPSC)

UNSPSC	39121307 Floor boxes
IGCC	4432 Floor boxes
Brand Name	Steel City
Type	Flush Service
Special Features	Fully adjustable
Application	Ideal for the modern office with workstations that have power, communications and data equipment
Material	Cast Iron

European Specifications (ETIM)

ETIM	EC000024 Installation box for underfloor-installation
Cover model	Rectangular
Suitable for wet cleaning	N
Suitable for hollow floor	Y
Material	Aluminium
With opening carpeting	N
Min. built-in depth	63.5mm
Colour	Other
Length external dimension	114.3mm
Width outside dimension	244.475mm

Packaging

Outer Quantity	2
Outer Dimensions (inches)	7.8x7.3x7.9
Weight Uom	6.87 lbs. Each

For further technical assistance, please contact us...

Thomas & Betts - USA
 8155 T&B Blvd.
 Memphis, TN 38125
 www.tnb.com

T&B Technical Support
 MS 3B-50
 8155 T&B Blvd.
 Memphis, TN 38125

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email:techsupport@tnb.com