



Representative

Catalog Number: SP6423/4 1 11/4TP2
Product ID: 7TAA003370R0013
UPC Number: 78599104013
Status: Active

Two Gang Flush Service Floor Box, 74 Cubic Inches, Length 4-1/2 Inches, Width 3 Inches, 3/4 Inch, 1 Inch, and 1-1/4 Inch Conduit Hubs, Cast Iron, Watertight, Adjustable, Concrete Applications Only, TP2

North American Specifications (UNSPSC)

UNSPSC	39121307 Floor boxes
IGCC	4432 Floor boxes
Brand Name	Steel City
Type	Two Gang Flush Service Floor Box
Special Features	Fully adjustable
Application	Ideal for the modern office with workstations that have power, communications and data equipment
Material	Cast Iron
Cubic Capacity	74 Cubic Inches

European Specifications (ETIM)

ETIM	EC000024 Installation box for underfloor-installation
Cover model	Rectangular
Suitable for wet cleaning	N
Suitable for hollow floor	Y
Material	Other
With opening carpeting	N
Min. built-in depth	88.9mm
Colour	Other
Length external dimension	114.3mm
Width outside dimension	244.475mm

Packaging

Outer Quantity	2
Outer Dimensions (inches)	7.8x7.3x8
Weight Uom	687 lbs. per 100

For further technical assistance, please contact us...

Thomas & Betts - USA
 8155 T&B Blvd.
 Memphis, TN 38125
www.tnb.com

T&B Technical Support
 MS 3B-50
 8155 T&B Blvd.
 Memphis, TN 38125

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com