



Representative

**Catalog Number:** SP644 3/4 1 TP2  
**Product ID:** 7TAA003370R0018  
**UPC Number:** 78599104022  
**Status:** Active

Four Gang Flush Service Floor Box, 148 Cubic Inches, Length 4-1/2 Inches, Width 3 Inches, 3/4 Inch and 1-1/4 Inch Conduit Hubs, Cast Iron, For Concrete Applications Only, TP2

### North American Specifications (UNSPSC)

UNSPSC	39121307 Floor boxes
IGCC	4432 Floor boxes
Brand Name	Steel City
Type	Four Gang Flush Service Floor Box
Special Features	Fully adjustable
Application	Ideal for the modern office with workstations that have power, communications and data equipment
Material	Cast Iron
Size	Length 4-1/2 Inches, Width 3 Inches, 3/4 Inch and 1-1/4 Inch Conduit Hub
Cubic Capacity	148 Cubic Inches
Knockouts	Yes

### European Specifications (ETIM)

ETIM	EC000024 Installation box for underfloor-installation
Cover model	Rectangular
Suitable for wet cleaning	N
Suitable for hollow floor	Y
Material	Other
With opening carpeting	N
Min. built-in depth	50.8mm
Colour	Other
Length external dimension	114.3mm
Width outside dimension	76.2mm

### Packaging

Outer Quantity	1
Outer Dimensions (inches)	15.2x5.4x7.3
Weight Uom	1325 lbs. per 100

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
 8155 T&B Blvd.  
 Memphis, TN 38125  
[www.tnb.com](http://www.tnb.com)

T&B Technical Support  
 MS 3B-50  
 8155 T&B Blvd.  
 Memphis, TN 38125

Hours: 7AM - 6PM CDT  
 Monday-Friday  
 Phone: (888) 862-3289  
 Fax: (901) 252-1321  
 Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)