



Actual

**Catalog Number:** XC-130-SAMPLE  
**Product ID:** 7TAA011070R0057  
**UPC Number:** 78599103988  
**Status:** Active

1/2 Inch. Snap-In Fittings for MC cable. Accommodates the widest range of MC cable size in the industry - 14-2 to 10-3 with ground. Suitable for use with steel and aluminum MC. High carbon steel zinc plated construction. For use in Dry locations. Cable diameter 0.46 to 0.54 inch. Temperature rating 105 degrees C. Sample of 5 pieces.

**North American Specifications (UNSPSC)**

UNSPSC	39121311 Electrical fittings
IGCC	4441 Electrical fittings
Brand Name	Steel City
Type	Saddle & Snap-In Connectors
Size	1/2 Inch
Material	Steel
Finish	Zinc

**Packaging**

Inner Quantity	1
Inner Dimensions (inches)	1x1x1
Outer Quantity	25
Outer Dimensions (inches)	18.25x7x10.62
Weight Uom	10 lbs. per 100

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
8155 T&B Blvd.  
Memphis, TN 38125  
www.tnb.com

T&B Technical Support  
MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email:techsupport@tnb.com