



Actual

**Catalog Number:** XC270-1  
**Product ID:** 7TAA010850R0262  
**UPC Number:** 78599102262  
**Status:** Active

Connector, Straight Squeeze-Type, Size 1/2 Inch, Clamping Range 0.74 Inch - 0.92 Inch, Length 1.43 Inch, Die Cast Zinc, Sold by Each

### North American Specifications (UNSPSC)

UNSPSC	39121419 Flex connectors
IGCC	4574 Squeeze Connectors
Brand Name	Steel City
Type	Squeeze Connectors
Size	1/2 Inch
Material	Zinc Die Cast

### European Specifications (ETIM)

ETIM	EC001180 Screw connection for protective metallic hose
Nominal size in inch	1/2 inch
Model	Straight
Revolving thread	N
Construction type	External thread
Connection type screw connection to housing	Thread
One-piece	Y
Material housing	Zinc die-cast
Surface protection	Untreated
Approved in combination with protective conduit DIN EN 61386-23	N
Approved in combination with protective conduit FI	N

### Packaging

Inner Quantity	25
Inner Dimensions (inches)	12.313x3.25x5
Outer Quantity	250
Outer Dimensions (inches)	15.4x13x10.9
Weight Uom	9.5 lbs. per 100

For further technical assistance, please contact us...

Thomas & Betts - USA  
 8155 T&B Blvd.  
 Memphis, TN 38125  
[www.tnb.com](http://www.tnb.com)

T&B Technical Support  
 MS 3B-50  
 8155 T&B Blvd.  
 Memphis, TN 38125

Hours: 7AM - 6PM CDT  
 Monday-Friday  
 Phone: (888) 862-3289  
 Fax: (901) 252-1321  
 Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)