



Actual

Catalog Number: XC280-1
Product ID: 7TAA010850R0267
UPC Number: 78599102263
Status: Active

Connector, Clamp Type, Size 3/8 Inch, Clamping Range 0.18 Inch - 0.64 Inch, Length 1.16 Inch, Die Cast Zinc, Bag of 1

North American Specifications (UNSPSC)

UNSPSC	39121311 Electrical fittings
IGCC	4441 Electrical fittings
Brand Name	Steel City
Type	Clamp Type Connectors
Application	For use with armored cable/flexible metal conduit
Standard	UL e23018
Size	3/8 Inch (1/2 Inch Knockout)
Material	Zinc Die Cast

European Specifications (ETIM)

ETIM	EC001180 Screw connection for protective metallic hose
Nominal size in inch	3/8 inch
Model	Straight
Revolving thread	N
Construction type	External thread
Connection type screw connection to housing	Thread
One-piece	Y
Material housing	Zinc die-cast
Surface protection	Untreated
Approved in combination with protective conduit DIN EN 61386-23	N
Approved in combination with protective conduit FI	N

Packaging

Inner Quantity	100
Inner Dimensions (inches)	11x6.375x5
Outer Quantity	400
Outer Dimensions (inches)	13.9x11.5x11.6
Weight Uom	6 lbs. per 100

Documents / Support Tools

Technical Data Sheet US	Available on Website
-------------------------	----------------------

For further technical assistance, please contact us...

Thomas & Betts - USA
 8155 T&B Blvd.
 Memphis, TN 38125
www.tnb.com

T&B Technical Support
 MS 3B-50
 8155 T&B Blvd.
 Memphis, TN 38125

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com