



Actual

**Catalog Number:** XF20/M20/C90/BL  
**Product ID:** 7TCA296060R0115  
**EAN Number:** 05020963015380  
**Status:** Active

90 Degree Elbow Fitting for Use with Xtraflex, Fixed External Male Thread, Nominal Conduit Size 20mm, M20 Thread, Polyamide (Nylon) 66, IP65, Black

### North American Specifications (UNSPSC)

UNSPSC	39121311 Electrical fittings
IGCC	4441 Electrical fittings
Brand Name	Adaptaflex
Type	Conduit Fitting with Metric Threads
Application	For Insertion into Threaded Entries or Knockout to Connect Conduit
Size	NC 20mm
Material	Polyamide/Nylon 6.6
Insulation Class	IP65
Color	Black
Connection	90 Degree
Cable Entry	M20 Thread

### European Specifications (ETIM)

ETIM	EC001178 Screw connection for protective plastic hose
Nominal diameter	20mm
Nominal size in inch	1/2 inch
Degree of protection (IP)	IP65
Model	90°-elbow
Revolving thread	N
Construction type	External thread
Type of connection	Thread
Thread connection size	M20 x 1.5
Thread length	13.5mm
One-piece	N
Material screw gland	Polyamide
Material sealing	No sealing
Colour	Black
Approved in combination with protective conduit DIN EN 61386-23	N
Approved in combination with protective conduit UR	N

### Packaging

Inner Quantity	10
Outer Quantity	120
Outer Dimensions (inches)	14x14x6
Weight Uom	0.04 lbs. Each

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
 8155 T&B Blvd.  
 Memphis, TN 38125  
 www.tnb.com

T&B Technical Support  
 MS 3B-50  
 8155 T&B Blvd.  
 Memphis, TN 38125

Hours: 7AM - 6PM CDT  
 Monday-Friday  
 Phone: (888) 862-3289  
 Fax: (901) 252-1321  
 Email:techsupport@tnb.com