



810058

LTC Preset Click-Type Torque Wrench - 3/8" Ratcheting Square Drive, 60 - 300 in-lb



PRODUCT DETAILS

- LTCR-Series torque wrenches have +/- 4% Indicated Value Accuracy from 20% to 100% of capacity, meeting or exceeding the requirements of ASME B107.300-2010 and ISO 6789
- When we preset the torque value for you at the factory, we include a free Certificate of Calibration from our ISO 17025 Accredited Lab
- Flattened case prevents side loading and provides support for the click mechanisms so the wrench is easier to calibrate and it hold calibration longer
- Cushioned comfort grip is lightweight and provides excellent ergonomics
- Slide pin ratchet provides strength and durability
- Easy to install ratchet renewal kit is available
- The torque is preset and locked in with a special tool
- Combination Adjusting and Release Tool (CART P/N 819177) allows the operator to easily adjust torque on all SLTC, LTC, LTCR and LTCS wrenches
- Torque can be set using any unit of measurement
- Can be ordered preset from the factory or you can set the torque with your own torque tester
- Wrench measures torque in the clockwise direction
- PLEASE NOTE: See below for manuals & details drawings; click the drop down menu, click on specific product PDF, click the download button

PRODUCT ATTRIBUTES

Product	MODEL	 N·m	 lb
810058	LTCR 300 I	6.8-24 N·m	1.0 lb