




810174

LTC Preset Click-Type Torque Wrench Fixed Square Drive, 360 - 1800 in,lbs

PRODUCT DETAILS

- LTCS Series torque wrenches have +/- 4% Indicated Value Accuracy from 20% to 100% of capacity, meeting or exceeding the requirements of ASME B107.300-2010 and ISO 6789
- When we preset the tool to your requested torque value we include a free Certificate of Calibration from our ISO 17025 Accredited Lab
- The low profile of the square drive creates access where other tools cannot go, which is important with our larger square drives
- Flattened case prevents side loading and provides support for the click mechanisms so the wrench is easier to calibrate and it hold calibration longer
- Cushioned comfort grip is lightweight and provides excellent ergonomics
- Slide pin ratchet provides strength and durability
- Easy to install ratchet renewal kit is available
- The torque is preset and locked in with a special tool
- Combination Adjusting and Release Tool (CART P/N 819177) allows the operator to easily adjust torque on all SLTC, LTC, LTCR and LTCS wrenches
- Torque can be set using any unit of measurement
- Can be ordered preset from the factory or you can set the torque with your own torque tester
- Wrench measures torque in the clockwise direction
- PLEASE NOTE: See below for manuals & details drawings; click the drop down menu, click on specific product PDF, click the download button

PRODUCT ATTRIBUTES

| Product | MODEL |  N·m |
|---------------|-------------|--|
| 810174 | LTCS 1800 I | 40.8-204 N·m |