



**810568**

**Adjustable Torque Screwdriver Kit -  
CAL 36/4 and CAL 40, 2 - 36 in-lb**



**PRODUCT DETAILS**

- Bi-directional Accuracy of +/- 6% Indicated Value from 20% to 100% of capacity
- Meets or exceeds ASME B107.300-2010 and ISO 6789
- Operator cannot over-torque, clutch releases automatically when desired torque has been achieved
- Scale on the shaft is marked in dual incrementation (in lb and Nm) on Cal 36/4, kgf•cm on CAL 40
- Magnifying lens improves the view of a clearly engraved scale
- To operate, simply dial torque setting and insert bit
- Anti-backlash design enhances repeatability
- Comes with FREE calibration certificate from our ISO/IEC 17025 Accredited Calibration Laboratory
- Kit includes Hex 5/64, 3/32, 7/64, 1/8, 9/64; PosiDriv 1, 2; Slotted 0-1, 3-4, 5-6, 8-10, 12-14; Torx T10, T15; Phillips 0, 1, 2, 3; Bit Holder 1/4"; Socket Adapter 1/4"
- Includes custom case

**PRODUCT ATTRIBUTES**

Product	MODEL	 lbf-in	 in-lb			
<b>810568</b>	CAL 36/4K	2-36 lbf-in	2 lbf-in	1/4 in	7.8 in	0.5 lb