



810574


LTC Preset Interchangeable Head Click-Type Torque Wrench, 150 - 300 in-lb



PRODUCT DETAILS

- +/- 4% repeatability from 20% to 100% of capacity
- Meets or exceeds the requirements of ASME B107.300-2010 and ISO 6789
- Tools preset at the factory include a free Certificate of Calibration from our ISO 17025 Accredited Lab
- Low profile of the square drive creates access where other tools cannot go
- Flattened case is sideloading resistant
- Error Proofing By Design flattened case provides superior mechanism support that makes the wrench easier to calibrate and it holds calibration much longer than other wrenches
- Excellent tactile and audible pulse when the preset torque is achieved
- Cushion grip plus lightweight for excellent ergonomics
- Fixed square drive provides exceptional strength and durability
- CART tool
- Torque is preset and locked in with a special tool
- Torque can be set using any unit of measurement
- Combination Adjusting and Release Tool (CART) P/N 819117 allows the operator to easily adjust torque on all SLTC -FM, SLTC, LTC, LTCR, and LTCS wrenches
- Can be ordered preset from the factory or you can set the torque with your own torque tester
- Wrench measures torque in the clockwise direction
- PLEASE NOTE: See below for manuals & details drawings; click the drop down menu, click on specific product PDF, click the download button

PRODUCT ATTRIBUTES

Product	MODEL	 N·m
810574	LTC 300 I OHT	40.8-204 N·m