







810855
Hardwired Preset Click-Type Torque Wrench (SLTC/SLTCR) Dovetail, 60 - 300 in-lb

PRODUCT DETAILS

- Accuracy of +/- 4% of the preset value from 20% to 100% of capacity
- Meets or exceeds requirements of ASME B107.300-2010 and ISO 6789
- Preset from the factory includes a free Certificate of Calibration from our ISO 17025 Accredited Lab
- Five of seven models use the incredibly strong SR dovetail and can be used with any of over 100 SR Interchangeable Heads
- Tamper-resistant torque setting mechanism design facilitates setting and discourages unauthorized torque setting changes
- Excellent audible and tactile impulse when preset torque is achieved
- Lightweight and cushion grip provides excellent ergonomics
- Slender body facilitates use in constrained-access applications
- Microswitch closes when the tool clicks and opens immediately when pressure is released
- Separate cable with a connector (required) facilitates replacement if damaged.
- PLEASE NOTE: See below for manuals & details drawings; click the drop down menu, click on specific product PDF, click the download button

PRODUCT ATTRIBUTES

Product	MODEL	 N·m	 lbf·in		
810855	SLTC 300 I - HARDWIRED	6.8-34 N·m	60-300 lbf·in		Dovetail