



815710


Dial Torque Wrench, 40- 200 Nm



PRODUCT DETAILS

- Accuracy of +/- 3% Indicated Value from 20% to 100% of capacity
- Meets or exceeds ASME B107.300-2010 and ISO 6789
- Includes free Certificate of Calibration from our ISO 17025 Accredited Lab
- Error Proofing By Design: Oversized dial face is extremely easy to read and helps to eliminate parallax error
- Glare-resistant dial cover makes it easy to read in difficult light conditions
- Error Proofing By Design: A memory indicator is provided on each wrench and remains at the maximum torque achieved for positive torque verification
- Heavy-duty dial guard protects against breakage
- Dial faces are color-coded: silver for inch-pounds, gold for foot-pounds, and white for Newton meters
- Wrenches with a capacity of up to 50 ft-lbs have a black powder-coated handle that provides an industrial-strength finish
- Wrenches with a capacity of 175 to 250 ft-lbs have a flexible PVC handle. The flexible PVC grip that comes on tools up to 250 ft. lbs. supports proper grip and provides comfort during use
- Wrenches with a capacity of 600 to 1000 ft-lbs have a specially designed extension aluminum handle that is easy to grip
- Each wrench comes in its own rugged, blow-molded, storage case
- FREE NIST-traceable tabulated certification included.
- PLEASE NOTE: See below for manuals & details drawings; click the drop down menu, click on specific product PDF, click the download button

PRODUCT ATTRIBUTES

Product	MODEL	 N·m	 Nm	 L	 lb
815710	IDW 200Nm FINAL ASSY	40-200 N·m	2.5 Nm	20.8 in	2.8 lb