



850227

Beam Torque Wrench - 1/2" , 60 - 300 ft-lb

PRODUCT DETAILS

- Incredibly durable design
- Exceptional accuracy retention permits extended calibration intervals and extremely low ownership cost
- Flat and Tapered Beam torque wrenches have a very low cost of ownership; they are virtually maintenance and repair-free
- Pivoted handle concentrates load at a precise point on the lever to assure torque accuracy
- Memory feature consists of pointers that follow a track on the scale and remain in place to indicate peak torque achieved
- Peak torque indicated on the scale is accurate even in destructive applications
- Bi-directional accuracy of +/- 2% of Indicated Value from 20% to 100% of capacity meets or exceeds requirements of ASME B107.300-2010 and ISO 6789
- Includes FREE certificate of calibration from our +/- .25% Indicated Value accuracy/ISO/IEC 17025 Accredited Calibration Laboratory
- PLEASE NOTE: See below for manuals & details drawings; click the drop down menu, click on specific product PDF, click the download button

PRODUCT ATTRIBUTES

Product	MODEL		 lbf·ft	 lb
850227	M 300	300 lbf·ft	10 lbf·ft	10.75 lb